# Vertiv<sup>™</sup> SmartCloset<sup>™</sup>

Rack Solutions Designed for IT & Network Closets



### When deploying IT at the Edge, physical infrastructure gets complicated fast.

Vertiv™ SmartCloset™ is a complete solution curated by Vertiv experts to enable rapid and risk-free IT deployments at the Edge.



### **Secure IT Rack**

Vertiv<sup>™</sup> VR Racks provide a secure, organized, and efficient place to manage critical IT infrastructure and enable edge locations to meet power and space requirements.



### **Emergency backup power**

Liebert® PSI5 and GXT5 UPS provide market-leading efficiency in line-interactive and online double-conversion topologies for power protection and voltage regulation. Also available with Lithium-ion UPS technology.



### **Remote Communications**

Networking cards enable integration of the UPS into monitoring systems, allowing users to manage system status and alarms 24/7 anywhere in the world.



### **Environmental Monitoring**

Help protect your critical IT infrastructure by strategically monitoring the temperature, humidity, and dew point within the network closet environment. Sensors are available only for some models.



### Integrated power distribution

Geist™ rPDUs give unmatched reliability, ultimate versatility, and piece of mind that the last link in your power chain is secure. Rack PDU's are available only for select models.



## Your investment protected with a system level warranty from Vertiv

We are here to support you with service solutions for your critical infrastructure and to ensure that your vital applications always work. The Vertiv SmartCloset has a full suite of service offerings to help protect your investment and your business.



#### **Seamless**

Solutions have been curated by Vertiv<sup>™</sup> to ensure compatibility of all components.

### **Simple**

Removes the guess work of matching physical infrastructure to the IT solution.

#### **Smart**

Power devices support network connectivity enabling remote management & monitoring from anywhere.

1

## **Technical Specifications - Entry Models**

| Network Closet<br>Bundle SKUs        | VSC42NX30PLANN                            | VSC42NX30PLAMV                            | VSC42NX30PLASV                            | VSC42NX30PLINN                            | VSC42NX30PLIMV                            | VSC42NX30PLISV                            |
|--------------------------------------|---|---|---|---|---|---|
| System Specifications                |   |   |   |   |   |   |
| W x D x H, mm (in)                   | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) |
| Weight, kg (lbs)                     | 159 (350)                                 | 166.5 (367)                               | 168 (371)                                 | 151 (334)                                 | 159 (350)                                 | 160 (354)                                 |
| Static load / Dynamic load, kg (lbs) | 1360 (3000) /<br>1022 (2250)              |
| U-Space (Usable)                     | 40U                                       | 40U                                       | 40U                                       | 40U                                       | 40U                                       | 40U                                       |
| rPDU Type                            | N/A                                       | Monitored                                 | Switched                                  | N/A                                       | Monitored                                 | Switched                                  |
| Usable Outlets, (rPDU)               | N/A                                       | (24) NEMA 5-20                            | (24) NEMA 5-20                            | N/A                                       | (24) NEMA 5-20                            | (24) NEMA 5-20                            |
| UPS Topology                         | Line Interactive                          |
| UPS Battery<br>Chemistry             | VRLA                                      | VRLA                                      | VRLA                                      | Lithium-ion                               | Lithium-ion                               | Lithium-ion                               |
| Usable Outlets, (UPS)                | (6) NEMA 5-20<br>(1) NEMA L5-30           | (6) NEMA 5-20                             | (6) NEMA 5-20                             | (6) NEMA 5-20<br>(1) NEMA L5-30           | (6) NEMA 5-20                             | (6) NEMA 5-20                             |
| Environmental<br>Monitoring          | N/A                                       | N/A                                       | Temperature<br>Humidity<br>Dew Point      | N/A                                       | N/A                                       | Temperature<br>Humidity<br>Dew Point      |
| Power Rating, VA                     | 3000                                      | 3000                                      | 3000                                      | 3000                                      | 3000                                      | 3000                                      |
| Max IT Load, Watts                   | 2700                                      | 2700                                      | 2700                                      | 2700                                      | 2700                                      | 2700                                      |
| Warranty and Service                 |   |   |   |   |   |   |
| Standard Warranty                    | 3-Year, System Level                      | 3-Year, System Level                      | 3-Year, System Level                      | 5-Year, System Level                      | 5-Year, System Level                      | 5-Year, System Level                      |
| Bill of Material                     |   |   |   |   |   |   |
| Rack                                 | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    |
| UPS                                  | PSI5-3000RT120                            | PSI5-3000RT120                            | PSI5-3000RT120                            | PSI5-3000RT120LI                          | PSI5-3000RT120LI                          | PSI5-3000RT120LI                          |
| rPDU                                 | N/A                                       | VP8832                                    | VP8932                                    | N/A                                       | VP8832                                    | VP8932                                    |
| Monitoring                           | IS-UNITY-SNMP                             | IS-UNITY-SNMP                             | IS-UNITY-SNMP                             | IS-UNITY-SNMP                             | IS-UNITY-SNMP                             | IS-UNITY-SNMP                             |
| Sensors                              | N/A                                       | N/A                                       | GTHD                                      | N/A                                       | N/A                                       | GTHD                                      |
| Rack Accessories                     | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        |



## **Technical Specifications - Value Models**

| Network Closet<br>Bundle SKUs        | VSC42NX30GLANN                            | VSC42NX30GLAMV                            | VSC42NX30GLASV                            | VSC42NX30GLINN                            | VSC42NX30GLIMV                            | VSC42NX30GLISV                            |
|--------------------------------------|---|---|---|---|---|---|
| System Specifications                |   |   |   |   |   |   |
| W x D x H, mm (in)                   | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) |
| Weight, kg (lbs)                     | 157 (346)                                 | 164 (362)                                 | 166 (366)                                 | 149 (329)                                 | 156 (345)                                 | 158 (349)                                 |
| Static load / Dynamic load, kg (lbs) | 1360 (3000) /<br>1022 (2250)              |
| U-Space (Usable)                     | 40U                                       | 40U                                       | 40U                                       | 40U                                       | 40U                                       | 40U                                       |
| rPDU Type                            | N/A                                       | Monitored                                 | Switched                                  | N/A                                       | Monitored                                 | Switched                                  |
| Usable Outlets, (rPDU)               | N/A                                       | (24) NEMA 5-20                            | (24) NEMA 5-20                            | N/A                                       | (24) NEMA 5-20                            | (24) NEMA 5-20                            |
| UPS Topology                         | Online Double-<br>Conversion              |
| UPS Battery<br>Chemistry             | VRLA                                      | VRLA                                      | VRLA                                      | Lithium-ion                               | Lithium-ion                               | Lithium-ion                               |
| Usable Outlets, (UPS)                | (6) NEMA 5-20<br>(1) NEMA L5-30           | (6) NEMA 5-20                             | (6) NEMA 5-20                             | (6) NEMA 5-20<br>(1) NEMA L5-30           | (6) NEMA 5-20                             | (6) NEMA 5-20                             |
| Environmental<br>Monitoring          | N/A                                       | N/A                                       | Temperature<br>Humidity<br>Dew Point      | N/A                                       | N/A                                       | Temperature<br>Humidity<br>Dew Point      |
| Power Rating, VA                     | 3000                                      | 3000                                      | 3000                                      | 3000                                      | 3000                                      | 3000                                      |
| Max IT Load, Watts                   | 2700                                      | 2700                                      | 2700                                      | 2700                                      | 2700                                      | 2700                                      |
| Warranty and Service                 |   |   |   |   |   |   |
| Standard Warranty                    | 3-Year, System Level                      | 3-Year, System Level                      | 3-Year, System Level                      | 5-Year, System Level                      | 5-Year, System Level                      | 5-Year, System Level                      |
| Bill of Material                     |   |   |   |   |   |   |
| Rack                                 | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    | VR3100                                    |
| UPS                                  | GXT5-3000LVRT2UXL                         | GXT5-3000LVRT2UXL                         | GXT5-3000LVRT2UXL                         | GXT5LI-<br>3000LVRT2UXL                   | GXT5LI-<br>3000LVRT2UXL                   | GXT5LI-<br>3000LVRT2UXL                   |
| rPDU                                 | N/A                                       | VP8832                                    | VP8932                                    | N/A                                       | VP8832                                    | VP8932                                    |
| Monitoring                           | RDU101                                    | RDU101                                    | RDU101                                    | RDU101                                    | RDU101                                    | RDU101                                    |
| Sensors                              | N/A                                       | N/A                                       | GTHD                                      | N/A                                       | N/A                                       | GTHD                                      |
| Rack Accessories                     | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        |

3



### **Technical Specifications - Premium Models**

| Network Closet Bundle SKUs           | VSC42NX50GLANN                            | VSC42NX50GLAMV                            | VSC42NX50GLASV                            |
|--------------------------------------|---|---|---|
| System Specifications                |   |   |   |
| W x D x H, mm (in)                   | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) | 600 x 1100 x 2000<br>(23.6 x 43.3 x 78.6) |
| Weight, kg (lbs)                     | 195 (429)                                 | 202 (446)                                 | 204 (449)                                 |
| Static load / Dynamic load, kg (lbs) | 37U                                       | 37U                                       | 37U                                       |
| U-Space (Usable)                     | 37U                                       | 37U                                       | 37U                                       |
| rPDU Type                            | N/A                                       | Monitored                                 | Switched                                  |
| Usable Outlets, (rPDU)               | N/A                                       | (36) C13, (6) C19                         | (24) C13, (4) C19                         |
| UPS Topology                         | Online Double-Conversion                  | Online Double-Conversion                  | Online Double-Conversion                  |
| UPS Battery Chemistry                | VLRA                                      | VLRA                                      | VLRA                                      |
| Usable Outlets, (UPS)                | (2) NEMA L6-30<br>(2) NEMA L6-20          | (1) NEMA L6-30<br>(2) NEMA L6-20          | (1) NEMA L6-30<br>(2) NEMA L6-20          |
| Environmental Monitoring             | N/A                                       | N/A                                       | Temperature<br>Humidity<br>Dew Point      |
| Power Rating, VA                     | 5000                                      | 5000                                      | 5000                                      |
| Max IT Load, Watts                   | 4600                                      | 4600                                      | 4600                                      |
| Warranty and Service                 |   |   |   |
| Standard Warranty                    | 3-Year, System Level                      | 3-Year, System Level                      | 3-Year, System Level                      |
| Bill of Material                     |   |   |   |
| Rack                                 | VR3100                                    | VR3100                                    | VR3100                                    |
| UPS                                  | GXT5-6KL630RT5UXLN                        | GXT5-6KL630RT5UXLN                        | GXT5-6KL630RT5UXLN                        |
| rPDU                                 | N/A                                       | VP8841                                    | VP8941                                    |
| Monitoring                           | RDU101<br>(Installed in UPS)              | RDU101<br>(Installed in UPS)              | RDU101<br>(Installed in UPS)              |
| Sensors                              | N/A                                       | N/A                                       | GTHD                                      |
| Rack Accessories                     | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        | VRA1014<br>VRA1005                        |

© 2023 Vertiv Group Corp. All rights reserved. Vertiv<sup>™</sup> and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.