Vertiv™ Reference Design

Knowledge to Build Optimized Infrastructure Solutions



Vertiv[™] Integrated Rack Solution

Reference Design #12

Premier Commercial and Office 15U Wall-Mount 1500VA Capacity

Solution Requirements

Physical Protection:

 Safeguard network gear from environmental threats and unauthorized access.

Power Protection:

 Prevent business interruption caused by power loss or power fluctuations with battery backup technology.

On-Site Management:

- Simplify deployment and support future growth with infrastructure designed for total compatibility and scalability.
- Recover business critical floor space with IT infrastructure designed with tight spaces in mind.

Remote Management

- Maintain peace of mind one or more remote sites are up and running with real-time notifications.
- Save time by remotely accessing and rebooting unresponsive network equipment without an on-site visit.

Site-Maintenance

- Ensure continuity of business with remote access and management of critical systems.
- Maximize your investment with on-site equipment maintenance and extended warranty protection.

Form Factor: Endpoint

Objective: Support network connectivity in small commercial and office environments.

Recommended Environment

Climate-controlled unsecure environment with air conditioning in place for human comfort where temperature, humidity, and air quality control challenges could put IT equipment at risk of damage from uncontrolled heat, dust, or moisture.

- Point-of-Sale Station
- Kiosk
- Converted Closet
- General Access Area
- Converted Closet



Integrated Solution Summary

Capacity	1500 VA / 1350 W	
Rack(s)	12U x 610mm x 610mm (HxWxD)	
Power Protection	Online Double Conversion	
Redundancy	N	
Power Distribution	Switched Unit Level 15A, 120V 1U horizontal. 6 NEMA 5-15R receptacles and NEMA 5-15P	
Cooling	Optional Upgrade	
Containment	Blanking Panels	
Monitoring	Included	
Services	Included	
Warranty	3 years	
Software	Included	

Explore all Commercial and Office form factors and power configurations available, Endpoint, Rack, and Row by visiting the Solution Builder on Vertiv.com or by contacting a Vertiv Sales Representative.

1



Integrated Solution Includes:

Qty:	Product Summary	SKU	Description:
1	Rack	202637G2	The Vertiv™ DWG Series is a 12U wall mount rack that secures and organizes network switches in closets and other locations with limited spaces. It accommodates switches and patch panels up to 26" deep. Adjustable depth front face 19" mounting rails (12U).
1	Cable and Airflow Management	VRA1000 VRA1008 VRA2000	Vertiv [™] VR Rack Accessories utilized to seamlessly integrate communications and power cables in to the cabinet while maintaining proper airflow separation of equipment intake and exhaust.
1	UPS	GXT5-1500LVRT2UXL	Vertiv™ Liebert® GXT5 UPS model GXT5-1500LVRT2UXL; 1500VA/1500W; 120VAC is an online double conversion UPS solution which offers premium power outage protection and continuous power conditioning in a compact and flexible rack/tower form factor.
1	UPS COMM Card	RDU101	The interface card delivers SNMP, Telnet and web-management capability for enhanced communications and control of Liebert® UPS. The card manages a wide range of operating parameters, alarms and notifications, transmitting data over the network. Environmental sensor data is provided via web and SNMP. Visit Vertiv.com for a free Vertiv™ Power Assist software download to gracefully shutdown an IT device when the UPS battery backup experiences a threatening condition.
1	Rack PDU	VP51100	Switched Unit Level Monitored Rack PDU VP51100 is a 15A, 120V 1U horizontal with input power monitoring and outlet level switching. It has 6 NEMA 5-15R receptacles and a NEMA 5-15P providing 1.4kW of power capacity. A Switched rPDU allows you to turn off outlets to avoid accidental overloads and remotely power cycle equipment to reboot unresponsive equipment. The unit is equipped with an environmental sensor port and dual ethernet ports.
1	IT Management	AV3108-001 ACS8008SAC-400	Vertiv [™] Avocent® AV3000 Rackmount KVM Over IP Switch CAC 8 Port KVM switches Local and Remote Access (AV3108-001). Vertiv [™] Avocent ACS 8000 8-port Serial Console Server, Single AC Power (ACS8008SAC-400).
1	Warranty and Service	PEPGXT-15005YR	Power Emergency Service Package provides 5 years of coverage for electronic parts and batteries, advanced replacement.
1	Software	DSV4.5-BASE DSV4.5-100DEV 1YRSLV-100DEV	Avocent® DSView delivers secured web-browser enabled sessions of on-network infrastructure controls. As an IT integrated solution, DSView delivers secured web-browser enabled sessions to Virtual Machines.

^{*}Additional accessories and components are required and included in the integrated solution. Contact a Vertiv Partner for the complete bill of materials, to receive pricing, and to purchase.

Recommended Upgrades

Qty:	Product Summary	Model #:	Description:
1	IT Management	ACS8008-LN-DAC	The Vertiv™ Avocent® ACS8000 Serial Console System delivers secure in-band and out-of-band visibility and control to downstream equipment in enterprise data centers, as well as cloud and colocation facilities. This serial console system serves as a secure management gateway and single point of entry keeping you connected to critical IT equipment even in the event of partial or total data center outages. Includes the upgraded Cellular capability.
1	Warranty and Service	PEPGXT-1500LF	Power Emergency Premier Package provides 5 years of coverage for electronic parts and batteries, advanced replacement. Also included: Remote diagnostic and preventive monitoring with Vertiv™ LIFE™ Services.
1	Software	ENVA-SERVER ENVA-DEV-100 ENVA-STUP-BSC ENVA-SERVER-SA ENVA-SA-100	Vertiv™ Environet™ Alert provides industry companies with critical facility monitoring software that is affordable and easy to use. This solution delivers superior monitoring, alerting, trending and data organization capabilities for companies in such verticals as healthcare, financial services, government and more, helping them protect and grow their business. Customers get monitoring, alerting and trending at a price that's right for their business.

Vertiv.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2021 Vertiv Group Corp. All rights reserved. Vertiv, and the Vertiv logo trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.