

OVERVIEW

Rack Transfer Switch (RTS) delivers redundant power to single corded devices. The RTS automatically detects the loss of power and switches the power load (no phase-syncronization required) to the alternative power source in less than 4-8 milliseconds without the need for human intervention.

Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.





Part #: VA4N2100

Model Number: AN03E1R0-10S203-2ST5ST5A011-D

Category: Rack Transfer Switch
Sub Category: Monitored Unit Level

Power Configuration: 20A, 120V, 1.9kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary: rPDU, Rack Transfer Switch Monitored Unit Level, 20A, 120V, 1.9kW, Horizontal, (10)

NEMA 5-20R, 10ft / 3m power cords with 5-20P, Black Powder Coat.

Monitoring: Input power monitoring. Environmental monitoring via optional remote sensors. Daisy

chain Ethernet connectivity. Local high visibility LED display.

Plug Form: Receptacle:





NEMA 5-20R (Quantity: 10)

Chassis Color Options:



Product Specification and Options

System Features

Monitoring	Input power monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
Power Switching	Auto Switching - In Event of Power Failure
Transfer Time	<4-8ms
Out of Phase Transfers	Yes
Front Panel HMI LED Overlay	Yes
Quantity Of Inputs	2 (Dual Input)
Voltage	100-120V
Current	20A
VA per Input (Load Capacity)	1.9kW (120V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	12/3
Power Cable Length	10ft / 3m
Power Entry Location	Left Rear
Plug Type	(2) NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Rear	10
- Style	Individual
- Voltage per Receptacle/Socket	120V
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable 4 Post Mounting (Range)	Yes (24" - 37")
Product Warranty	5-year limited warranty if registered within 120 days of
•	purchase, otherwise warranty defaults to 3 years

Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Chassis Dimensions (HxWxD)	1.72in x 17in x 18in / 44mm x 432mm x 457mm
Shipped Weight	17lbs (7.71kg)