

Vertiv™ Liebert® GXT5 Lithium-Ion 5-10kVA 120/208V Rack-Tower GUIDE SPECIFICATIONS

1.0 GENERAL

1.1 Summary

This specification shall define the electrical and mechanical characteristics and requirements for a continuous-duty, single-phase, solid state uninterruptible power system (UPS). The UPS shall provide high quality AC power for sensitive electronic equipment loads.

1.2 Standards

The UPS shall be designed in accordance with applicable sections of the current revision of the following documents. Where a conflict arises between these documents and statements made herein, the statements in this specification shall govern.

- Listed to UL 1778, 5th Edition; and c-UL Listed
- UL 1973 & UL 1642 (for battery pack and cell)
- IEC62619 Edition 1.0 (for battery pack and cell)
- CSA 22.2 No. 107.3
- ANSI C62.41, Category B
- IEC 61000-3-2
- IEC 61000-3-12
- EN62040-2
- EN61000-4-2
- EN61000-4-3
- EN61000-4-4
- EN61000-4-5
- EN61000-4-6
- FCC Part 15, Class A
- ISTA Procedure 2A/3E
- RoHS2 (6 by 6) Compliant
- REACH and WEEE Compliant

1.3 System Description

1.3.1 Modes of Operation

The UPS shall be designed to operate as a true on-line double-conversion system in the following modes:

1. **Normal** - In normal operation incoming AC power shall be fed to the input power factor corrected (PFC) rectifier that converts the AC power to DC power for the inverter. In this mode, power shall also be derived from utility power for the battery charger. The inverter shall derive DC power from the PFC rectifier to regenerate filtered and regulated AC sinewave power for the connected load. The unit shall begin charging the battery once the UPS is connected to utility power, regardless of whether the UPS is ON or OFF. In the event of a utility outage or severe abnormality (sag or swell), the inverter shall support the connected load from battery power until the battery is discharged or the utility power returns, whichever occurs first.

2. **Battery** - Upon failure of utility/mains AC power, the critical AC load shall be supplied by the inverter, which obtains power from the battery. There shall be no interruption in power to the critical load upon failure or restoration of the utility/mains AC source.
3. **Recharge** - Upon restoration of utility/mains AC power, after a utility/mains AC power outage, the input converter shall automatically restart and resume supplying power to the inverter and the battery charger begins to recharge the battery.
4. **Automatic Restart** - Upon restoration of utility/mains AC power, after a utility/mains AC power outage and complete battery discharge, the UPS shall automatically restart and resume supplying power to the critical load and the battery charger automatically recharges the battery. This feature shall be capable of being disabled by the user.
5. **Bypass** - The integral bypass shall perform an automatic transfer of the critical AC load from the inverter to the bypass source, in the event of an overload, PFC failure, internal over temperature, DC bus overvoltage or inverter failure conditions.
6. **ECO** – The UPS shall allow the user to enable and place the UPS in ECO mode of operation to reduce electrical consumption. The ECO mode operation shall be an Active type, whereas the UPS will power the connected equipment through the bypass path and the UPS inverter shall be on and operating at no load in order to stay synchronized to the bypass to ensure rapid transfers to inverter power when input power falls outside of the user customizable parameters. The UPS shall also have a user customizable requalification time that input power must remain within the ECO mode parameters before transferring back to ECO operation. This is to minimize the number of transfers between bypass and inverter.

1.3.2 Design Requirements

1. Voltage

Shall operate at either 120/208V or 120/240V by sensing the utility phase angle and configuring the dual inverters to the same angle: 120 or 240 degrees (or) 180 degrees. Nominal input/output voltage specifications of the UPS at rated load shall be:

a. Input

The UPS shall be able to operate from 120/208V, 50/60 Hz (or) 120/ 240V, 50/60 Hz without the use of selector switches or voltage taps. Input wiring must be 3-wire plus ground (L1, L2, N, G, with N solid bonded to G at the distribution panel).

b. Output

Output voltage shall be present at terminals L1, L2, and N. The output voltage shall be 120/208V, 50/60 Hz. Voltage measured between L1-N and L2-N: 120 VAC \pm 3%, 50/60 Hz; L1-L2: 208 VAC \pm 5%, 50/60 Hz. The UPS shall be configurable using the included configuration program to provide the following alternate output voltages: 120/240V, 127/220V, 115/230V, 110/220V, 100/200V, all voltages 50 or 60 Hz. If the UPS is started on battery with no input power present, the default output voltage shall be 120/208V, 60 Hz from the factory. After the UPS has been started from utility, the output voltage/frequency shall match the last known input voltage/frequency that was applied.

2. Output Load Capacity

GXT5LI-5000MVRT3UXLN

VA	Watts	PF	VAC Output
2500	2500	1.0	110 / 115 / 120 / 125
2500	2250	1.0	100
5000	5000	1.0	120 / 208, 125 / 220 (120 or 240 degree only), 110 / 220, 115 / 230, 120 / 240 (180 degree only)
5000	4500	0.9	100 / 200 (180 degree only)

GXT5LI-6000MVRT3UXLN

Input Connector	VA	Watts	PF	VAC Output
Terminal Block	3000	3000	1.0	115 / 120 / 125
	3000	2700	0.9	110
	2850	2565	0.9	100
	6000	6000	1.0	120 / 208, 125 / 220 (120 or 240 degree only), 115 / 230, 120 / 240 (180 degree only)
	6000	5400	0.9	110 / 220 (180 degree only)
	5700	5130	0.9	100 / 200 (180 degree only)
Plug	3000	2700	0.9	120 / 125
	2900	2610	0.9	115
	2750	2475	0.9	110
	2500	2250	0.9	100
	6000	5400	0.9	120 / 208, 125 / 220 (120 or 240 degree only), 120 / 240 (180 degree only)
	5800	5220	0.9	115 / 230 (180 degree only)
	5500	4950	0.9	110 / 220 (180 degree only)
	5000	4500	0.9	100 / 200 (180 degree only)

GXT5LI-8000MVRT4UXLN

VA	Watts	PF	VAC Output
4000	4000	1.0	100 / 110 / 115 / 120 / 125
8000	8000	1.0	120 / 208, 125 / 220 (120 or 240 degree only), 100 / 200, 110 / 220, 115 / 230, 120 / 240 (180 degree only)

GXT5LI-10KMVRT4UXLN

VA	Watts	PF	VAC Output
5000	5000	1.0	115 / 120 / 125
5000	4500	0.9	110
4750	4275	0.9	100
10000	10000	1.0	120 / 208, 125 / 220 (120 or 240 degree only), 115 / 230, 120 / 240 (180 degree only)
10000	9000	0.9	110 / 220 (180 degree only)
9500	8550	0.9	100 / 200 (180 degree only)

3. Included Battery

The UPS battery shall utilize Lithium Iron Phosphate (LiFePO₄) cells.

4. Reserve Time

Internal battery reserve times below shall be at full load with ambient temperature of 77 °F (25°C) with resistive loading.

- **5,000VA:** 12 minutes
- **6,000VA:** 9.5 minutes
- **8,000VA:** 12.5 minutes
- **10,000VA:** 9.5 minutes

These times shall be at full rated load with new fully charged batteries at an ambient temperature of 77 °F (25 °C) and resistive loading.

5. Battery Recharge

The UPS shall contain a four-stage battery charger designed to prolong battery life. Recharge time for UPS included battery shall be less than 2 hours to 90% capacity after a complete discharge into full load.

1.3.3 Performance Requirements

1. AC Input to UPS

- a. **Voltage:** The point at which the UPS transfers to battery operation shall be dependent on the amount of load that the UPS is supporting. The UPS shall operate from the following voltage ranges without drawing power from the batteries:
 - Low Line Voltage Range
 - From 0 to 50% load the low line voltage shall be constant.
 - From 51-100% load the low line voltage shall increase at a linear rate.
 - For loads over 100%, the low line voltage remains constant.

Load		5-6-8 kVA Models	10 kVA Model
		Low Line Voltage	Low Line Voltage
> 101%	L-N Transfer	90 ± 3.1 VAC	100 ± 3.1 VAC
	L-N Comeback	98 ± 3.1 VAC	108 ± 3.1 VAC
51% to 100%	L-N Transfer	60 - 90 ± 3.1 VAC	60 - 100 ± 3.1 VAC
	L-N Comeback	68 - 98 ± 3.1 VAC	68 - 108 ± 3.1 VAC
50% to 0%	L-N Transfer	60 ± 3.1 VAC	60 ± 3.1 VAC
	L-N Comeback	68 ± 3.1 VAC	68 ± 3.1 VAC

High Line Voltage Range	
High Line Voltage	120/208V Models
High Line Transfer	149.5 ± 3.1 VAC
High Line Comeback	142.5 ± 3.1 VAC

- b. **Frequency:** The UPS shall auto-sense input frequency when first powered up and shall operate within the following frequency specifications. UPS shall be capable of cold start with default frequency of 60 Hz. Once started the frequency operating window shall be 40-70 Hz. Three frequency settings shall be available in the Liebert GXT5 Configuration program: Auto frequency sensing (factory default setting), 50 Hz frequency conversion and 60 Hz frequency conversion.
- c. **Input Power Factor:** >0.99 lagging at rated load.
- d. **Input Current Harmonic Distortion:** THD shall be less than or equal to 3% at linear, full load operation. THD shall be less than or equal to 5% at nonlinear, full load operation.
- e. **Input Current Ratings**

UPS Model	Input	VAC (L-N/L-L)	Max Amps
GXT5LI-5000MVRT3UXLN	L14-30P	100/200 – 125/217	24
GXT5LI-6000MVRT3UXLN	Terminal Block	100/200 – 125/217	32
GXT5LI-8000MVRT4UXLN	Terminal Block	100/200 – 125/217	48
GXT5LI-10KMVRT4UXLN	Terminal Block	100/200 – 125/217	55

- f. **Inrush Current (initial startup, no load):** The UPS shall have a maximum inrush current of 6 times the full load peak input current.
- g. **Surge Immunity & Protection:** UPS shall conform to ANSI C62.41, Category B
- h. **Surge Protection:** Metal oxide varistors (MOV) ratings shall be 190V, 80 Joules minimum each connected L1-L2, L1-G, and L2-G.

2. AC Output, UPS Inverter

- a. **Voltage Configuration:** 120/208 VAC at 120 degrees phase angle factory-default, 50/60 Hz, single-phase, 3-wire-plus-ground (L-L-N-G). Optional output voltage settings shall be user-adjustable. Output options shall include 100/200, 110/220, 115/230, 120/208, 120/240, and 125/220 VAC.
- b. **Voltage Regulation:** Voltage regulation shall be ± 1% steady state.

- c. **Frequency Regulation:** ± 3.5 Hz synchronized to bypass. ± 0.1 Hz free running or on-battery operation.
- d. **Frequency Slew Rate:** Slew rate shall be 1.0 Hz per second maximum. The slew rate shall be user-selectable for non-parallel units, options to be 0.2, 0.5, or 1.0 Hz/S. For parallel units, the slew rate shall be fixed at 0.2 Hz per second.
- e. **Voltage Distortion:** <2% total harmonic distortion (THD) typical into a 100% linear load, <5% THD typical into a 100% non-linear load. For parallel units, <3% total harmonic distortion (THD) typical into a 100% linear load, <6% THD typical into a 100% non-linear load.
- f. **Load Power Factor Range:** The load power factor range shall be 0.65 lagging to 1.0 (unity) without power derating.
- g. **Output Power Rating:** Output power rating shall be 5kVA/5kW, 6kVA/6kW, 8kVA/8kW, 10kVA/10kW
- h. **Load Crest Factor:** The UPS will handle a 100% non-linear load having a crest factor of 3:1 without performance degradation.
- i. **Inverter Overload Capability**

Overload Percent	Duration Inverter shall Support Rated Load
<105%	Continuous
105.1% to 125%	5 minutes
125.1% to 150%	60 seconds
>150.1%	Minimum of 200ms

- j. **Voltage Transient Response:** The transient response of the output voltage with resistor step loading will be $\pm 5\%$ for input supply from off to on and for a load from 0% to 100% and 100% to 0%. Transient response in the output voltage with resistor step loading will be $\pm 4\%$ for input supply from off to on and for a load from 20% to 100% and 100% to 20%.
- k. **Transient Recovery Time:** To nominal voltage within 60ms.
- l. **AC-AC Efficiency:** The UPS shall be EPA Energy Star 2.0 qualified and labeled.

The UPS shall be EPA Energy Star 2.0 qualified and labeled.

- GXT5LI-5000MVRT3UXLN: 93% AC –AC at full rated linear load
- GXT5LI-6000MVRT3UXLN: 93% AC –AC at full rated linear load
- GXT5LI-8000MVRT4UXLN: 94% AC –AC at full rated linear load
- GXT5LI-10KMVRT4UXLN: 94% AC –AC at full rated linear load

1.4 Environmental Conditions

1. Ambient Temperature

Operating: The ambient temperature range, when UPS is operational, shall be from 32 °F to 104 °F (0 °C to 40 °C). There shall not be any degradation in the performance when operating in this range. Automatic derating shall occur for operation in higher ambient temperatures based on the following table.

Temperature	Derating
105.8 °F (41 °C)	99%
107.6 °F (42 °C)	98%
109.4 °F (43 °C)	97%
111.2 °F (44 °C)	96%
113.0 °F (45 °C)	95%
114.8 °F (46 °C)	94%
116.6 °F (47 °C)	93%
118.4 °F (48 °C)	92%
120.2 °F (49 °C)	91%
122.0 °F (50 °C)	90%

Storage: -4 °F to 140 °F (-20 °C to 60 °C)

2. Relative Humidity

- Operating: 0 to 95% non-condensing.
- Storage: 0 to 95% non-condensing.

3. Altitude: 9843 ft. (3000 m) max., without power derating when operated within the temperature specified in Section 1.4, Item 1. Ambient temperature shall be derated 9 °F (5 °C) for each additional 1640 ft. (500 m) above 9843 ft. (3000 m).

4. Audible Noise: The audible noise when measured at 1 meter from front, sides, or rear shall be 58 dBA maximum.

1.5 User Documentation

The specified UPS system shall be supplied with Safety Instruction & Warning Sheet with WEEE recycling information (ISO 14001 compliance), printed copy of quick installation guide, and printed copy of factory test report. The user manual shall be available as a download from the manufacturer's public web site that includes installation instructions, a functional description of the equipment with block diagrams, safety precautions, illustrations, step-by-step operating procedures, and general maintenance guidelines.

1.6 Warranty

The UPS manufacturer shall warrant the UPS against defects in materials and workmanship for five (5) years. The no-hassle replacement warranty shall include shipping costs to the customer site for the new replacement unit and shipping costs from the customer site for the return of the failed unit. The manufacturer's standard warranty shall cover all parts, including the battery.

1.7 Quality Assurance

1.7.1 Manufacturer Qualifications

More than 40 years of experience in the design, manufacture, and testing of solid-state UPS systems shall be required. The manufacturer shall be certified to ISO 9001:2008.

1.7.2 Factory Testing

Before shipment, the manufacturer shall fully and completely test the system to ensure compliance with the specification.

2.0 PRODUCT

2.1 Fabrication

All materials and components making up the UPS shall be new, of current manufacture and shall not have been in prior service except as required during factory testing. All relays shall be provided with dust covers.

2.1.1 Wiring

Wiring practices, materials and coding shall be in accordance with the requirements of the standards listed in Section 1.2 and other applicable codes and standards. All wiring shall be copper.

2.1.2 Cabinet

The UPS system shall be composed of input rectifier/PFC converter, IGBT inverter, battery charger, input filter and internal bypass circuit; and batteries consisting of the appropriate number of Lithium-Ion battery cells. The UPS and Battery cabinets shall be housed in a rack-tower NEMA type 1 enclosure and shall meet the requirements of IP20. The UPS and battery cabinets shall be cleaned and painted RAL 7021 Black. Unit dimensions and weights shall be (rack mount orientation):

Model	Unit Dimensions W x D x H, in. (mm)	Unit Weight lb. (kg)
GXT5LI-5000MVRT3UXLN	16.9 x 25.6 x 5.0 (430 x 800 x 127.5)	125.6 (57.0)
GXT5LI-6000MVRT3UXLN	16.9 x 25.6 x 5.0 (430 x 800 x 127.5)	125.6 (57.0)
GXT5LI-8000MVRT4UXLN	16.9 x 25.6 x 6.69 (430 x 800 x 170)	224.8 (102)
GXT5LI-10KMVRT4UXLN	16.9 x 25.6 x 6.69 (430 x 800 x 170)	224.8 (102)

2.1.3 Cooling

The UPS shall be forced-air cooled by an internally mounted, continuously operating fan. Fan speed shall be controlled by the UPS. Air intake shall be through the front of the unit and exhausted out the rear of the unit.

2.2 Components

2.2.1 Input Converter

1. General

Incoming AC power shall be converted to a regulated DC output by the input converter supplying DC power to the inverter. The input converter shall provide input power factor correction (PFC) and input current distortion reduction.

2. AC Input Current Limit

The input converter shall be provided with AC input current limiting whereby the maximum input current is limited to 125% of the full load input current rating.

3. Input Protection

The UPS shall have built-in protection against under voltage, over current and overvoltage conditions including low-energy lightning surges, introduced on the primary AC source. The UPS shall be able to sustain input surges without damage per criteria listed in ANSI C62.41, Category B, Level 3.

4. Battery Recharge

The UPS shall contain a three-stage battery charger designed to prolong battery life. Recharge time for the included UPS battery shall be less than 2 hours maximum to 90% capacity (full-load discharge rate). There shall be DC overvoltage protection so that if the DC voltage exceeds the pre-set limit, the UPS will shut down automatically and the critical load will be transferred to bypass.

2.2.2 Inverter

1. General

The UPS inverter shall be a pulse width modulated (PWM) design capable of providing the specified AC output. The inverter shall convert DC power from the input converter output or the battery into precise sinewave AC power for supporting the critical AC load.

2. Overload

The inverter shall be capable of supplying current and voltage for overloads exceeding 100% and up to 200% of full load current. A visual indicator and audible alarm shall indicate overload operation. For greater currents or longer time duration, the inverter shall have electronic current limiting protection to prevent damage to components. The inverter shall be self protecting against any magnitude of connected output overload. Inverter control logic shall sense and disconnect the inverter from the critical AC load without the requirement to clear protective devices.

3. Inverter DC Protection

The inverter shall be protected by the following DC shutdown levels:

- DC Overvoltage Shutdown
- DC Under voltage Shutdown (End of Discharge)
- DC Under voltage Warning (Low Battery Reserve); factory default set at 2 minutes (user configurable 2 to 30 minutes).

4. Output Frequency

An oscillator shall control the output frequency of the UPS. The inverter shall maintain the output frequency to ± 0.1 Hz of nominal frequency during Battery mode, Frequency Converter mode or when otherwise not synchronized to the utility/mains source.

5. Output Protection

The UPS inverter shall employ electronic current limiting circuitry.

6. Battery Over Discharge Protection

To prevent battery damage from over discharging, the UPS control logic shall automatically raise the shutdown voltage set point, depending on output load and connected battery system at the onset of battery operation.

2.2.3 Display and Controls

1. General

The UPS shall be provided with a microprocessor-based unit status display and controls section designed for convenient and reliable user operation. The monitoring functions such as voltages, currents, UPS status and alarm indicators shall be displayed on a full color graphical LCD display.

2. System

UPS display shall also include LED based system indicators. The system level indicators shall be: run indicator, and alarm indicator.

Indicator	LED Color	LED State	Indication
Run Indicator	Green	On	UPS has output
		Blinking	Inverter is starting
		Off	UPS has no output
Alarm Indicator	Yellow	On	Alarm occurs
	Red	On	Fault occurs
	N/A	Off	No alarm, no fault

3. Controls

UPS startup and shutdown operations shall be accomplished by using power button on the front panel of the UPS. The display shall be menu driven navigation and use four control buttons for ease of navigation and selection of the configurable parameters.

a. Control Buttons

The UPS display control button functionality shall be as follows:

- **ESC button:** This button shall return to the previous menu or abort any change before confirming the change.
- **Up/Left arrow button:** This button shall move the cursor up or left, or increase the value displayed when changing parameters. This button shall also be used to scroll up for navigating the screens.
- **Down/Right arrow button:** This button shall move the cursor down or right, or decrease the value displayed when changing parameters. This button shall also be used to scroll down for navigating the screens.
- **Enter button:** This button shall enter the next level menu or confirm the parameter changes.

b. Display Menu Structure

The UPS display shall have the following menu structure with the following status and configuration screens.

UPS Flow Screen (Default screen)

The UPS flow screen shall be the default screen after system startup. It shall display an overview screen showing status information, the active (green) power path, and non-working power path (gray). Details in this default screen include operating mode, the input voltage and frequency; output voltage and

frequency; battery capacity and estimated battery time remaining; load percentage. To prolong display life, the UPS LCD display will dim and display a screen saver after two minutes of no user interaction if there is no active alarm. Pressing the ENTER button shall wake up the display and this action shall not perform any operation. If an alarm or fault occurs, the display shall also wake immediately.

Main Menu

The main menu shall list 6 submenu selections, from left to right, then top to bottom:

- Status
- Settings
- Control
- Log
- About
- Maintenance

Status

The UPS status screens shall provide the following information:

- Input
- L-N voltage (V)
- L-N current (A)
- Frequency (Hz)
- Power Factor
- Energy (kWh)
- Input black count (count of input voltage lost)
- Input brown count (count of PFC overload to battery)
- Bypass
- L-N voltage (V)
- Frequency (Hz)
- Battery
- Battery status
- Battery voltage (V)
- Battery current (A)
- Backup time (min)
- Remaining capacity (%)
- Discharge count (number of discharges for the battery module)
- Total discharge time (min)
- Batt running time (day)
- Battery replacement time (date of last replacement)
- External battery cabinet group No.
- Battery average temp (°C)
- Battery highest temp (°C)
- Battery lowest temp (°C)
- Output
- L-N voltage (V)
- L-N current (A)
- Frequency (Hz)
- Energy (kWh)

- Load
- Sout (apparent output power, kVA)
- Pout (active output power, kVA)
- Power Factor
- Load Percent (%)
- Time Since Startup
- Days / Hours / Minutes

Settings

The UPS Configuration screens shall provide the following customizable parameters, where default values are listed first:

- Output
- Voltage selection
- Startup on Bypass (Enable/Disable)
- Frequency Selection (Auto bypass Enable/Auto bypass disable/50 Hz no bypass/60 Hz no bypass)
- Bypass voltage upper limit
- Bypass voltage lower limit
- Run mode (normal mode, or ECO mode)
- ECO voltage range
- ECO frequency range
- ECO requalification time
- Battery
- External Battery AH
- External battery cabinet group No. (0-10)
- Low Battery time
- Battery replaced time
- Battery periodic test enable
- Batt. Note duration (month)
- Discharge protect time
- Equal charge enable
- Max charge current
- Temperature compensation
- Replace Battery

Monitor

- Language
- Date
- Time
- Display Orientation (Auto-rotate, rack, tower)
- Audible Alarm (enable/disable)
- Change settings password

System

- Auto restart
- Auto restart delay

- Guaranteed shutdown
- Start with no battery
- Remote control
- Any mode shutdown auto restart enable
- Output contact NO/NC
- Input contact NO/NC
- Dry contact 5 output (Low battery, On bypass, On battery, UPS fault)
- Dry contact 6 output (Low battery, On bypass, On battery, UPS fault)
- Dry contact 1 output (Low battery, On bypass, On battery, UPS fault)
- Dry contact 2 output (Low battery, On bypass, On battery, UPS fault)
- Sleep mode
- IT system compatibility
- Outlet Parameter Options
- Apply same settings across outlets
- Turn on Outlet
- Turn on Delay
- Outlet Settings Based on Discharging Time
- Threshold of turning off the outlet
- Turn on when power returns
- Outlet Settings Based on Backup Time
- Threshold of turning off the outlet
- Turn on when power returns
- Outlet Settings Based on Capacity
- Threshold of turning off the outlet
- Turn on when power returns

Control

The UPS shall have the following controls from the display:

- UPS ON/OFF/Bypass
- Turn UPS ON
- Turn UPS OFF
- Turn ON Bypass (manually transfer to bypass power)
- Audible Alarm
- Turn audible alarm ON (test alarm)
- Turn audible alarm OFF (alarm silence)
- Battery Test
- Start battery self-test
- Clear Faults
- Reset Power Statistics

Log

The UPS shall have an event log to record 255 events and shall be viewable from the display:

- View Log
- Navigate the event log to view the last 255 events.
- The event log once full will begin to replace the first event logged to provide a FIFO process for maintaining event history. The event history shall record and display the number of events out of

the 255 (xxx/255) as well as the time (days, hours, mins) from when viewing the event and the event that occurred.

About

The UPS shall have an About screen to display the UPS model number, serial number, time since startup, hardware version, and firmware version.

Maintenance

The UPS shall have the ability to display the network information of the RDU101 SNMP/webcard when installed. Information available includes MAC address and IP address.

4. Automatic Battery Test

The UPS shall feature an automatic battery test with the factory default test interval set at every 8 weeks. The battery test shall ensure the capability of the battery to supply power to the inverter while loaded. If the battery fails the test, the UPS shall display a warning message to indicate the internal batteries need replaced. The Automatic Battery test feature shall be capable of being disabled or configured to operate every 8, 12, 16, 20, or 26 weeks through the UPS Configuration Program or from the LCD display.

2.3 Automatic Internal Bypass

2.3.1 General

A bypass circuit shall be provided as an integral part of the UPS. The bypass shall have a make-before-break transfer, shall have a maximum detect and transfer time of 4-6 milliseconds and shall be a double-pole device. The bypass circuit shall be designed to ensure the simultaneous transfer of the L1 and L2 poles. The bypass shall be configured to wrap around the PFC converter, battery charger, DC-DC converter, inverter, and battery. The bypass circuit shall use the rear panel mounted UPS input circuit breaker and route bypass power through the UPS input filters and surge suppression circuit. The bypass circuit default position shall be in the Bypass mode (utility).

2.3.2 Automatic Transfers

The transfer control logic shall activate the bypass automatically, transferring the critical AC load to the bypass source, after the transfer logic senses one of the following conditions:

- UPS overload
- UPS over temperature
- PFC failure
- Inverter failure
- DC bus overvoltage

Once the overload condition is reduced, the load shall be automatically transferred back to inverter power. An over temperature requires manual transfer back to inverter power after cooling.

2.4 Optional External Battery Cabinet

- 5-6kVA models shall allow connection of up to eight VEBCLI-192VRT1U external battery cabinets to provide extended run time capabilities.
- 8-10kVA models shall allow the connection of up to eight pairs (sixteen total) VEBCLI-192VRT1U external battery cabinets to provide extended run time capabilities.

2.5 Output Distribution

Output power distribution shall be hardwired output as standard. Power output distribution is available with break-before-make maintenance bypass switch to allow for complete shutdown and isolation of the UPS for service without powering down the connected loads.

2.6

2.6 Communication Options

2.6.1 Vertiv™ Liebert® IntelliSlot™ Communication Port

5-10 kVA GXT5 LI UPS shall include one Liebert® IntelliSlot™ communication port with one Liebert® IntelliSlot™ RDU101 card factory installed. Alternate networking cards will require field removal of the RDU101 card and field installation of the alternate networking card. The Vertiv™ Liebert® GXT5 UPS supports the below networking cards.

a. Vertiv™ Liebert® IntelliSlot™ RDU101 Communications Card

The Liebert® IntelliSlot™ RDU101 card shall deliver SNMP and web access to the UPS via 10/100 Mb/s ethernet port. This card shall enable remote or local field upgrades of the SNMP firmware, and managed device firmware and configuration updates. This card shall support environmental monitoring via Liebert® SN Sensors.

b. Vertiv™ Liebert® IntelliSlot™ Relay Interface Card (IS-RELAY)

The optional Liebert® IntelliSlot™ Relay Interface Card shall provide contact closure for remote monitoring of alarm conditions in the UPS, delivering signals for On Battery, On Bypass, Low Battery, Summary Alarm, UPS Fault, and On UPS. The contacts shall be rated for 24 VAC or 24VDC at 1A. Connections shall be to a terminal block connector with cable provided by the end user.

2.6.2 Terminal Block Connections

The UPS shall contain on the rear panel a terminal block to provide low voltage signals for On Battery, Low Battery, Any Mode Shutdown, and Battery Mode Shutdown

2.6.3 Any-mode Shutdown

The purpose of Any-Mode Shutdown shall be to shut down the UPS output by turning Off the rectifier, inverter, and bypass so that there is no power to the loads.

Any-Mode Shutdown can be operated locally and remotely, as described as follows:

- Local Any-mode Shutdown can be entered from the battery mode shutdown device on the back of the unit.
- Remote Any-mode Shutdown can be initiated by a battery mode shutdown button mounted at a remote location.

Remote Power Off shall be performed either by NO or NC contact of Any-mode Shutdown, depending on the settings in the configuration program. A current-limited source (+12VDC, 50mA) shall be available from the UPS. The connection to the UPS for remote connection shall be via terminal block connector. Any-mode Shutdown wiring shall conform to all national, regional, and local wiring regulations.

2.6.4 Battery Mode Shutdown

- Battery Mode Shutdown shall permit shutting down the UPS by turning Off the rectifier, inverter and bypass so that there is no power to the load when the UPS is on Battery. Battery Mode Shutdown shall be able to be performed locally or remotely.
- Local Any-Mode Shutdown can be entered from the battery mode shutdown device on the back of the unit.
- Remote Any-Mode Shutdown can be initiated by a battery mode shutdown button mounted at a remote location.
- The actuation of the battery mode shutdown shall be logged as an event in the event history log.
- Remote power off shall be performed by a NC/NO contact.
- The remote connection shall be provided via terminal block connector.
- A 12Vdc, 50mA current limited source shall be available from the UPS for relay drive.
- The battery shutdown signal will not cause an immediate shutdown, it will instead start a 2 minute shutdown timer. This timer cannot be stopped once it is triggered. If the utility voltage returns during this count down timer then the UPS will still shutdown and must remain shut down for 10 seconds. The auto-restart setting shall then dictate whether the UPS turns back ON when the power is restored.
- Battery mode Shutdown wiring shall conform to all national, regional, and local wiring regulations.

2.6.5 USB Port

The USB communications port (Version 2.0) shall meet the HID Power Device standard, version 1.0 or later. All models shall work with the Power Management system in Microsoft Windows XP or later. They shall also support the equivalent functions in Linux, and Mac OSX.

2.6.6 Serial Port

A serial port (RS-232) shall be provided on the rear of the UPS, with an RJ-45 connector. This connector shall enable use of the Vertiv UPS Command Line Interface.